

Compact cylinder ADNGF-2"-3"-P-A

Part number: 557260

FESTO



Data sheet

Feature	Value
Stroke	3 in
Piston diameter	2"
Based on standard	ISO 21287
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Design	Piston Piston rod Profile barrel
Position detection	Via proximity switch
Protection against torque/guide	Guide rod with yoke
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-4 °F...176 °F
Impact energy in end positions	0.738 ft-lbf
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	238 lbf
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	265 lbf
Moving mass for 0 mm stroke	10.2 oz
Additional moving mass per 10 mm stroke	2.27 oz
Basic weight for 0 mm stroke	24.3 oz
Additional weight per 10 mm stroke	1.03 oz
Type of mounting	Either: With through-hole Via female thread With accessories
Pneumatic connection	1/8 NPT
Material collar screws	Steel
Material cover	Anodised wrought aluminium alloy

Feature	Value
Material seals	NBR
Material dynamic seals	TPE-U(PU)
Material end plate	Anodised wrought aluminium alloy
Material piston rod	High-alloy steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy