

Coupling
EAMD-67-82-25-32X32-U
Part number: 558007



Data sheet

Feature	Value
Mounting diameter 1	25 mm
Mounting diameter 2	32 mm
Size	67
Nominal length	82 mm
Mounting position	optional
Max. rotational speed	4500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	831 kgmm ²
Transmittable torque	150 Nm
Product weight	1557 g
Note on materials	RoHS-compliant