


Motor flange
EAMF-A-48A-60G/H
Part number: 558019

FESTO



Data sheet

Feature	Value
Mounting position	optional
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-10 °C...60 °C
Product weight	158 g
Interface code, motor in	60G 60H
Interface code, clutch housing	48A
Note on materials	RoHS-compliant