



Mini slide

EGSL-BS-55-250-12.7P

Part number: 559339

FESTO



Data sheet

Feature	Value
Working stroke	250 mm
Size	55
Running parallelism along Z-axis	0.1 mm
Parallelism	0.125 mm
Reversing backlash theoretical	50 µm
Spindle diameter	12.7 mm
Spindle pitch	12.7 mm/U
Mounting position	optional
Guide	Ball bearing cage guide
Design	Electric mini slide Guidance With ball screw drive
Type of motor	Stepper motor Servo motor
Spindle type	Ball screw drive
Position detection	Via proximity switch
Max. acceleration	25 m/s ²
Max. speed	1 m/s
Repetition accuracy	±0.015 mm
Duty cycle	100%
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Sound pressure level	65 dB(A)
Degree of protection	IP40
Ambient temperature	0 °C...60 °C
Continuous feed force	200 N
Max. drive torque	1.017 Nm
Max. force F _y	563 N
Max. force F _z	563 N
Max. moment M _x	27 Nm
Max. moment M _y	33 Nm
Max. moment M _z	33 Nm

Feature	Value
Max. radial force at drive shaft	260 N
Max. feed force Fx	300 N
Frictional torque independent of load	0.13 Nm
Reference value effective load, horizontal	10 kg
Reference value effective load, vertical	10 kg
Mass moment of inertia JL per kg of working load	0.041 kgcm ²
Mass moment of inertia JO	0.2327 kgcm ²
Feed constant	12.7 mm/U
Maintenance interval	Life-time lubrication
Moving mass	1740 g
Product weight	4050 g
Type of mounting	Via female thread Via centring sleeve With accessories
Note on materials	RoHS-compliant
Material cover	Die-cast aluminium Painted
Material guide rail	Rolled steel
Material housing	Wrought aluminium alloy Anodised
Material yoke plate	Wrought aluminium alloy Anodised
Material ball screw nut	Rolled steel
Material spindle	Rolled steel