

# Solenoid coil VACC-S13-18-A1-2U

Part number: 562891

**FESTO**



## Data sheet

| Feature                                      | Value   |
|--|---|
| Type of actuation                            | Electric  |
| Mounting position                            | optional  |
| Switching position indicator                 | no  |
| Duty cycle                                   | 100%  |
| Insulation material class                    | H   |
| Characteristic coil data                     | 110 V DC: 1.8 W<br>110 V AC: 50/60 Hz, power 1.8 VA |
| Permissible voltage fluctuations             | -15%/+10%   |
| CE mark (see declaration of conformity)      | To EU Low Voltage Directive                         |
| UKCA marking (see declaration of conformity) | To UK regulations for electrical equipment          |
| Corrosion resistance class CRC               | 4 - Very high corrosion stress                      |
| LABS (PWIS) conformity                       | VDMA24364 zone III                                  |
| Degree of protection                         | IP65  |
| Ambient temperature                          | -20 °C...60 °C                                      |
| Product weight                               | 210 g   |
| Electrical connection                        | Type A<br>Plugs<br>To EN 175301-803                 |
| Note on materials                            | RoHS-compliant                                      |
| Material solenoid coil                       | PA<br>UP  |