

Guide axis ELFR-...-35- -

Part number: 571435

FESTO



Data sheet

Feature	Value
Working stroke	50 mm...800 mm
Size	35
Mounting position	optional
Guide	Plain-bearing guide Recirculating ball bearing guide
Design	Passive guide axis
Max. acceleration	50 m/s ²
Max. speed	1 m/s...3 m/s
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP20
Ambient temperature	-10 °C...50 °C
2nd moment of area Iy	3770 mm ⁴
2nd moment of area Iz	4190 mm ⁴
Max. force Fy	50 N
Max. force Fz	50 N
Max. idle running transfer resistance	3 N
Reference service life	5000 km
Additional moving mass per 10 mm stroke	0 g
Basic weight for 0 mm stroke	1200 g
Additional weight per 10 mm stroke	23 g
Material profile	Wrought aluminium alloy Anodised
Note on materials	RoHS-compliant
Material drive cover	Wrought aluminium alloy Anodised
Material guide rail	Steel
Material slide	Wrought aluminium alloy Anodised