

Manifold rail VABM-L1-...

Part number: 573605

FESTO



Data sheet

Feature	Value
Grid dimension	10.5 mm 16 mm 19 mm
Mounting position	optional
Max. number of valve positions	24
Approval	c UL us - Recognized (OL)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Product corresponds to the internal product definition from Festo for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 6 according to ISO 14644-1
Storage temperature	-20 °C...60 °C
Pilot air port 12/14	M5
Pilot exhaust port 82/84	M5
Pneumatic connection, port 1	G1/8 G1/4 G3/8
Pneumatic connection, port 2	M5 M7 G1/8 G1/4
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy