

# Electrical sub-base VAVE-L1-1VR8-LP

Part number: 573919

FESTO



## Data sheet

| Feature                         | Value                                        |
|---------------------------------|----------------------------------------------|
| Reverse polarity protection     | Bipolar                                      |
| Additional functions            | Spark arresting                              |
| Signal status display           | LED                                          |
| Nominal operating voltage DC    | 12 V<br>24 V                                 |
| Immunity to surge               | 0.8 kV                                       |
| Pollution degree                | 3                                            |
| Corrosion resistance class CRC  | 2 - Moderate corrosion stress                |
| LABS (PWIS) conformity          | VDMA24364-B2-L                               |
| Degree of protection            | IP65                                         |
| Ambient temperature             | -5 °C...60 °C                                |
| Mounting position               | optional                                     |
| Max. tightening torque          | 0.27 Nm                                      |
| Product weight                  | 3.2 g                                        |
| Electrical connection           | 3-pin/2-pin<br>M8/-<br>Plug connector/socket |
| Protective conductor connection | Not available                                |
| Type of mounting                | On solenoid valve via self-tapping screw     |
| Housing colour                  | Black                                        |
| Note on materials               | RoHS-compliant                               |
| Material cover                  | PA                                           |
| Material seals                  | EPDM                                         |
| Material housing                | PA                                           |
| Material screws                 | Tempered steel                               |