

Stopper cylinder DFSP-16-15-PS-PA

Part number: 576061

FESTO



Data sheet

Feature	Value
Stroke	15 mm
Piston diameter	16 mm
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Single-acting Pulling
Design	Piston Piston rod Profile barrel
Position detection	Via proximity switch
Protection against torque/guide	Round piston rod
Operating pressure	0.28 MPa...1 MPa 2.8 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...80 °C
Impact force	880 N
Permissible lateral force during switching operation	147 N
Max. cycle frequency	5 Hz
Type of mounting	With through-hole Via female thread With accessories Either:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material collar screws	High-alloy stainless steel
Material cover	Wrought aluminium alloy Anodised
Material seals	TPE-U(PU)
Material piston rod	High-alloy stainless steel

Feature	Value
Material roll	Galvanised steel
Material cylinder barrel	Wrought aluminium alloy Smooth anodised