


Electric drive ESBF-BS-50-200-20P

Part number: 8022598

FESTO



Data sheet

Feature	Value
Working stroke	200 mm
Size	50
Stroke	200 mm
Piston rod thread	M16x1.5
Reversing backlash theoretical	40 µm
Spindle diameter	20 mm
Spindle pitch	20 mm/U
Torsional backlash at piston rod +/-	0.15 deg
Based on standard	ISO 15552
Mounting position	optional
Piston-rod end	Male thread
Type of motor	Stepper motor Servo motor
Position detection	Via proximity switch
Design	Electric cylinder with ball screw
Spindle type	Ball screw
Protection against torque/guide	With plain-bearing guide
Max. acceleration	25 m/s ²
Max. rotational speed	3600 rpm
Max. speed	1.33 m/s
Repetition accuracy	±0.01 mm
Duty cycle	100%
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...60 °C
Suitable for use with food	See supplementary material information
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	0 °C...60 °C
Max. drive torque	16.3 Nm
Max. radial force at drive shaft	300 N
Max. feed force Fx	5000 N

Feature	Value
Frictional torque independent of load	0.3 Nm
Reference value effective load, horizontal	500 kg
Reference value effective load, vertical	500 kg
Mass moment of inertia JH per metre of stroke	1.1387 kgcm ²
Mass moment of inertia JL per kg of working load	0.1013 kgcm ²
Mass moment of inertia JO	0.2203 kgcm ²
Maintenance interval	Life-time lubrication
Moving mass for 0 mm stroke	793 g
Additional moving mass per 10 mm stroke	35 g
Basic weight for 0 mm stroke	1982 g
Additional weight per 10 mm stroke	65 g
Type of mounting	Via female thread Or accessories
Interface code, actuator	D50
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy, smooth anodised
Material piston rod	High-alloy stainless steel
Material screws	Galvanised steel
Material spindle nut	Rolled steel
Material spindle	Rolled steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy