

Electric drive ESBF-...-50- -

Part number: 8022601

FESTO



Data sheet

Feature	Value
Size	50
Stroke	30 mm...1000 mm
Piston rod thread	M16x1.5
Spindle diameter	20 mm
Torsional backlash at piston rod +/-	0.15 deg
Based on standard	ISO 15552
Mounting position	optional
Type of motor	Stepper motor Servo motor
Position detection	Via proximity switch
Design	Electric cylinder with ball screw Electric cylinder with lead screw spindle
Variants	Metals with copper, zinc or nickel by mass as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Protection against torque/guide	With plain-bearing guide
Duty cycle	100%
Corrosion resistance class CRC	2 - Moderate corrosion stress 3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitability for the production of Li-ion batteries	Product corresponds to the internal product definition from Festo for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 7 according to ISO 14644-1
Storage temperature	-20 °C...60 °C
Suitable for use with food	See supplementary material information
Relative air humidity	0 - 95%
Degree of protection	IP40 IP65
Ambient temperature	0 °C...60 °C
Max. radial force at drive shaft	300 N

Feature	Value
Max. feed force Fx	5000 N
Frictional torque independent of load	0.3 Nm
Type of mounting	Via female thread Or accessories
Interface code, actuator	D50
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy, smooth anodised
Material piston rod	High-alloy stainless steel
Material screws	Galvanised steel
Material spindle nut	Rolled steel
Material spindle	Rolled steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy