


# Pressure sensor SPAW-P16R-G14F-2PV-M12

Part number: 8022799

**FESTO**



## Data sheet

Feature	Value
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Note on materials	RoHS-compliant
Measured variable	Relative pressure
Measurement method	Metal thin-film pressure sensor
Start value for pressure measuring range	0 MPa 0 bar 0 psi
End value for pressure measuring range	1.6 MPa 16 bar 232 psi
Overload pressure	3.2 MPa 32 bar 464 psi
Operating medium	Compressed air to ISO 8573-1:2010 [---] Liquid media Gaseous media
Media temperature	-20 °C...85 °C
Ambient temperature	0 °C...80 °C
Accuracy in ± % FS	1 %FS
Repetition accuracy in ± %FS	0.15 %FS
Switching output	2xPNP
Switching function	Freely programmable
Switching element function	Switchable
Max. output current	250 mA
Analogue output	0 - 10 V
Rise time	3 ms
Short circuit current rating	yes
Operational voltage range DC	15 V...35 V
Reverse polarity protection	For operating voltage

Feature	Value
Electrical connection 1, connection type	Plugs
Electrical connection 1, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 1, number of connections/cores	5
Electrical connection 1, type of mounting	Screw-type lock
Type of mounting	Via female thread With accessories
Mounting position	optional
Pneumatic connection	Female thread G1/4
Product weight	230 g
Material housing	ABS High-alloy stainless steel
Material in contact with the medium	High-alloy stainless steel
Display type	4-place alphanumeric LED indicator
Displayable units	MPa bar kPa kg/cm <sup>2</sup> psi
Switching status indication	Red LED
Setting options	Via display and keys
Protection against tampering	PIN code
Setting range threshold value	0.5 %...100 %
Setting range hysteresis	0.5 %...99.5 %
Degree of protection	IP65 IP67
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III