


Pressure sensor

SPAN-P10R-R18M-PN-PN-L1

Part number: 8035547

FESTO



Data sheet

| Feature | Value |
|----------------------------------------------|-------------------------------------------------------------------------------|
| Approval | RCM trademark c UL us listed (OL) |
| CE mark (see declaration of conformity) | To EU EMC Directive In accordance with EU RoHS Directive |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC To UK RoHS instructions |
| Certificate issuing authority | UL E322346 |
| Note on materials | RoHS-compliant |
| Measured variable | Relative pressure |
| Measurement method | Piezoresistive pressure sensor |
| Start value for pressure measuring range | 0 MPa 0 bar 0 psi |
| End value for pressure measuring range | 1 MPa 10 bar 145 psi |
| Max. overload pressure | 15 bar |
| Overload pressure | 1.5 MPa 15 bar 217.5 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases |
| Note on operating and pilot medium | Lubricated operation possible |
| Media temperature | 0 °C...50 °C |
| Ambient temperature | 0 °C...50 °C |
| Accuracy in ± % FS | 1.5 %FS |
| Repetition accuracy in ± %FS | 0.3 %FS |
| Temperature coefficient in ± %FS/K | 0.05 %FS/K |
| Switching output | 2 x PNP or 2 x NPN, switchable |
| Switching function | Window comparator Threshold value comparator Auto difference monitoring |
| Switching element function | N/C or N/O contact, switchable |
| Max. output current | 100 mA |
| Short circuit current rating | yes |

| Feature | Value |
|------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Operational voltage range DC | 15 V...30 V |
| Reverse polarity protection | For all electrical connections |
| Electrical connection 1, connection type | Plugs |
| Electrical connection 1, connector system | Connection pattern L1) |
| Electrical connection 1, number of connections/cores | 4 |
| Type of mounting | Front panel mounting Via thread Via wall/surface bracket |
| Mounting position | optional |
| Pneumatic connection | Male thread R1/8 Female thread M5 |
| Product weight | 46 g |
| Material housing | PA-reinforced |
| Material in contact with the medium | FPM High-alloy stainless steel |
| Display type | Illuminated LCD |
| Displayable units | MPa bar inH2O inHg kPa kgf/cm ² mbar mmHg psi |
| Setting options | Teach-in Via display and keys |
| Protection against tampering | PIN code |
| Setting range threshold value | 0 %...100 % |
| Setting range hysteresis | 0 %...90 % |
| Degree of protection | IP40 |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Suitability for the production of Li-ion batteries | Product corresponds to the internal product definition from Festo for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils |
| Cleanroom class | Class 4 according to ISO 14644-1 |