



# Toothed belt axis ELGC-TB-KF-60-1200

Part number: 8062782

FESTO



## Data sheet

| Feature  | Value  |
|--|--|
| Effective diameter of drive pinion                 | 24.83 mm   |
| Working stroke                                     | 1200 mm  |
| Size   | 60   |
| Stroke reserve                                     | 0 mm   |
| Toothed-belt pitch                                 | 3 mm   |
| Mounting position                                  | optional   |
| Guide  | Recirculating ball bearing guide   |
| Design   | Electromechanical linear axis<br>With toothed belt   |
| Type of motor                                      | Stepper motor<br>Servo motor   |
| Position detection                                 | Via proximity switch<br>Via inductive sensors  |
| Max. acceleration                                  | 15 m/s <sup>2</sup>  |
| Max. speed   | 1.5 m/s  |
| Repetition accuracy                                | ±0.1 mm  |
| Duty cycle   | 100%   |
| LABS (PWIS) conformity                             | VDMA24364 zone III   |
| Suitability for the production of Li-ion batteries | Product corresponds to the internal product definition from Festo for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils |
| Cleanroom class                                    | Class 7 according to ISO 14644-1   |
| Storage temperature                                | -20 °C...60 °C   |
| Degree of protection                               | IP40   |
| Ambient temperature                                | 0 °C...50 °C   |
| Impact energy in end positions                     | 0.25 mJ  |
| Note on the impact energy in the end positions     | At maximum homing speed of 0.01 m/s  |
| 2nd moment of area Iy                              | 441000 mm <sup>4</sup>   |
| 2nd moment of area Iz                              | 542000 mm <sup>4</sup>   |
| Max. drive torque                                  | 1.49 Nm  |
| Max. force Fy                                      | 3641 N   |

| Feature   | Value  |
|---|--|
| Max. force Fz   | 3641 N   |
| Max. force Fy total axis  | 600 N  |
| Max. force Fz total axis  | 1800 N   |
| Fy at theoretical life value of 100 km (only guide consideration) | 13400 N  |
| Fz at theoretical life value of 100 km (only guide consideration) | 13400 N  |
| Max. idle running transfer resistance                             | 15.6 N   |
| Max. moment Mx  | 29.1 Nm  |
| Max. moment My  | 31.8 Nm  |
| Max. moment Mz  | 31.8 Nm  |
| Max. moment Mx total axis   | 29.1 Nm  |
| Max. moment My total axis   | 31.8 Nm  |
| Max. moment Mz total axis   | 31.8 Nm  |
| Mx at theoretical life value of 100 km (only guide consideration) | 107 Nm   |
| My at theoretical life value of 100 km (only guide consideration) | 117 Nm   |
| Mz at theoretical life value of 100 km (only guide consideration) | 117 Nm   |
| Distance between slide surface and guide centre                   | 54.6 mm  |
| Max. feed force Fx  | 120 N  |
| Frictional torque independent of load                             | 0.194 Nm   |
| Torsional mass moment of inertia It                               | 29800 mm <sup>4</sup>  |
| Mass moment of inertia JH per metre of stroke                     | 0.0851 kgcm <sup>2</sup>   |
| Mass moment of inertia JL per kg of working load                  | 1.5411 kgcm <sup>2</sup>   |
| Mass moment of inertia JO   | 0.8804 kgcm <sup>2</sup>   |
| Feed constant   | 78 mm/U  |
| Reference service life  | 5000 km  |
| Maintenance interval  | Life-time lubrication  |
| Moving mass   | 482 g  |
| Weight of slide   | 139 g  |
| Product weight  | 6878 g   |
| Basic weight for 0 mm stroke                                      | 1775 g   |
| Additional weight per 10 mm stroke                                | 43 g   |
| Dynamic deflection (moving load)                                  | 0.05% of the axis length, max. 0.5 mm                                    |
| Static deflection (load in standstill)                            | 0.1% of the axis length  |
| Interface code, actuator  | T42  |
| Material end cap  | Painted die cast aluminium   |
| Material profile  | Anodised wrought aluminium alloy   |
| Note on materials   | RoHS-compliant   |
| Material cover tape   | Stainless steel strip  |
| Material drive cover  | Painted die cast aluminium   |
| Material guide slide  | Steel  |
| Material guide rail   | Steel  |
| Material pulleys  | High-alloy stainless steel   |
| Material slide  | Die-cast aluminium   |
| Material toothed belt   | Polychloroprene oder Nitrilkautschuk (NBR) mit Glascord und Nylonüberzug |