


**Axial kit**  
**EAMM-A-L62-120G**  
Part number: 8063507



**Data sheet**

| Feature                  | Value                 |
|--------------------------|-----------------------|
| Nominal length           | 76.9 mm               |
| Mounting position        | optional              |
| Max. rotational speed    | 5500 rpm              |
| LABS (PWIS) conformity   | VDMA24364-B2-L        |
| Storage temperature      | -25 °C...60 °C        |
| Relative air humidity    | 0 - 95%               |
| Degree of protection     | IP40                  |
| Ambient temperature      | -10 °C...60 °C        |
| Mass moment of inertia   | 151 kgmm <sup>2</sup> |
| Transmittable torque     | 47 Nm                 |
| Product weight           | 1970 g                |
| Interface code, actuator | L62                   |
| Interface code, motor in | 120G                  |
| Note on materials        | RoHS-compliant        |