


# Guide axis ELFC-KF-32-600

Part number: 8062801

FESTO



## Data sheet

Feature	Value
Working stroke	600 mm
Size	32
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Guidance
Position detection	Via proximity switch Via inductive sensors
Max. acceleration	15 m/s <sup>2</sup>
Max. speed	1.5 m/s
Duty cycle	100%
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitability for the production of Li-ion batteries	Product corresponds to the internal product definition from Festo for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 7 according to ISO 14644-1
Degree of protection	IP40
Ambient temperature	0 °C...50 °C
2nd moment of area I <sub>y</sub>	38000 mm <sup>4</sup>
2nd moment of area I <sub>z</sub>	45000 mm <sup>4</sup>
Max. force F <sub>y</sub>	356 N
Max. force F <sub>z</sub>	356 N
Max. moment M <sub>x</sub>	1.3 Nm
Max. moment M <sub>y</sub>	1.1 Nm
Max. moment M <sub>z</sub>	1.1 Nm
Max. force F <sub>y</sub> total axis	150 N
Max. force F <sub>z</sub> total axis	300 N
Max. moment M <sub>x</sub> total axis	1.3 Nm
Max. moment M <sub>y</sub> total axis	1.1 Nm
Max. moment M <sub>z</sub> total axis	1.1 Nm
Torsional mass moment of inertia I <sub>t</sub>	1770 mm <sup>4</sup>

Feature	Value
Displacement force	2 N
Reference service life	5000 km
Maintenance interval	Life-time lubrication
Fy at theoretical life value of 100 km (only guide consideration)	1310 N
Fz at theoretical life value of 100 km (only guide consideration)	1310 N
Mx at theoretical life value of 100 km (only guide consideration)	5 Nm
My at theoretical life value of 100 km (only guide consideration)	4 Nm
Mz at theoretical life value of 100 km (only guide consideration)	4 Nm
Moving mass	61 g
Basic weight for 0 mm stroke	168 g
Additional weight per 10 mm stroke	11 g
Dynamic deflection (moving load)	0.05% of the axis length, max. 0.5 mm
Static deflection (load in standstill)	0.1% of the axis length
Material end cap	Painted die cast aluminium
Material profile	Anodised wrought aluminium alloy
Note on materials	RoHS-compliant
Material cover tape	High-alloy stainless steel
Material guide slide	Steel
Material guide rail	Steel
Material slide	Die-cast aluminium