

Dispense head

VT0E-8-D8-T3-M22C-08-V-S-PC-M

Part number: 8063635

FESTO



Data sheet

| Feature | Value |
|--|---|
| Valve function | 2/2-way, closed, monostable |
| Operating pressure | 0 MPa...0.05 MPa 0 bar...0.5 bar 0 psi...7.25 psi |
| Internal volume | 113 µl valve with fluid connections |
| Nominal size | 0.8 mm |
| Nominal width of dosing needle | 0.6 mm |
| Length of dosing needle | 30 mm |
| Grid dimension | 9 mm |
| Sealing principle | Soft |
| Mounting position | optional |
| Type of reset | Mechanical spring |
| Type of piloting | Direct |
| Water flow rate at max. operating pressure | 1300 µl/s |
| Min. dosing volume | 3 µl |
| Note on dosing volume | Depends on configuration, environment and application |
| Typical dosing precision | <1% CV für Volumina > 5 µl <2.5% CV for volumes between 1-5 µl |
| Note on dosing precision | Depends on configuration, environment and application |
| Max. switching frequency | 4 Hz |
| Note on switching frequency | Dependent on the ambient temperature and installation state |
| Switching time on | 7 ms |
| Note on switching time on | Depends on configuration, environment and application |
| Switching time off | 2 ms |
| Note on switching time off | Depends on configuration, environment and application |
| Duty cycle | 50% (max. switch-on time 1 s) |
| Electrical power consumption | 1.8 W |
| Information on power consumption | Specification per valve |
| Nominal operating voltage DC | 24 V |
| Permissible voltage fluctuations | +/- 10 % |
| Medium | Liquid media |
| Note on the medium | Observe resistance of materials that come into contact with the media |

| Feature | Value |
|-------------------------------------|---|
| Instructions on use | See application note (available on the Support Portal at festo.com) |
| Vibration resistance | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -20 °C...70 °C |
| Media temperature | 5 °C...50 °C |
| Degree of protection | IP30 |
| Note on degree of protection | In assembled state |
| Ambient temperature | 5 °C...40 °C |
| Product weight | 220 g |
| Electrical connection | 9-pin Plugs Sub-D |
| Type of mounting | Via through-hole for M3 screw Via female thread and centring sleeve Either: |
| Fluid connection | 8x UNF1/4-28 |
| Note on fluid connection | Fitting enclosed for tubing with 3 mm outside diameter |
| Material of dosing needle | High-alloy stainless steel |
| Material number of dosing needle | 1.4301 |
| Note on materials | RoHS-compliant |
| Material in contact with the medium | ETFE FPM PC PEEK PPS High-alloy stainless steel |
| Type of actuation | Electric |
| Nominal altitude of use | <= 2000 m NHN |
| Relative air humidity | 0 - 95% Non-condensing |
| Pollution degree | 2 |