


# Shock absorber DYSS-G8-2-4-Y1F

Part number: 8073911

**FESTO**



## Data sheet

| Feature                                | Value                         |
|----------------------------------------|-------------------------------|
| Size                                   | 2                             |
| Stroke                                 | 4 mm                          |
| Cushioning                             | Self-adjusting                |
| Mounting position                      | optional                      |
| Position detection                     | Without                       |
| Max. impact speed                      | 0.5 m/s                       |
| Reset time at room temperature         | 0.5 s                         |
| Reset time at min. ambient temperature | 1 s                           |
| Mode of operation                      | Pushing<br>Single-acting      |
| Corrosion resistance class CRC         | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity                 | VDMA24364-B2-L                |
| Ambient temperature                    | -10 °C...70 °C                |
| Cushioning length                      | 4 mm                          |
| Max. stop force                        | 60 N                          |
| Max. tightening torque                 | 0.5 Nm                        |
| Max. energy consumption per stroke     | 0.1 J                         |
| Max. energy consumption per hour       | 270 J                         |
| Max. residual energy                   | 0.003 J                       |
| Reset force                            | 0.7 N                         |
| Min. insertion force                   | 2.5 N                         |
| Product weight                         | 3.9 g                         |
| Load range                             | 0.8 kg                        |
| Type of mounting                       | Via threaded sleeve           |
| Note on materials                      | RoHS-compliant                |
| Material seals                         | NBR                           |
| Material housing                       | High-alloy steel              |
| Material piston rod                    | High-alloy steel              |