

# Compact cylinder AEN-S-20-5-I-P-A

Part number: 8076502

**FESTO**



## Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	20 mm
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Pushing
Piston-rod end	Female thread
Design	Piston Piston rod
Position detection	Via proximity switch
Variants	Piston rod at one end
Operating pressure	0.06 MPa...1 MPa 0.6 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Impact energy in end positions	0.055 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	13 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	162 N
Moving mass for 0 mm stroke	18 g
Additional moving mass per 10 mm stroke	6 g
Basic weight for 0 mm stroke	65 g
Additional weight per 10 mm stroke	26 g
Type of mounting	With through-hole Via female thread With accessories Either:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Anodised wrought aluminium alloy

Feature	Value
Material dynamic seals	NBR TPE-U(PU)
Material housing	Anodised wrought aluminium alloy
Material piston rod	High-alloy stainless steel