

Connecting cable NEBA-

Part number: 8078221

FESTO



Data sheet

Feature	Value
Conforms to standard	EN 61076-2-101 EN 61076-2-104 EN 61984
Approval	c UL us listed (OL)
Intended use	The connecting cable connects field devices (sensors, actuators) with controllers.
Frequency of connection	100
Product weight	22 g...373 g
Instructions on use	Meets the requirements of IEC 61010-1 and 61010-2-202, in particular for electrically operated valves from Festo. Only energy-limited circuits with a maximum current of 4 A at a max. open circuit voltage of 30 V DC are permissible for supplying electrically actuated valves from Festo.
Electrical connection 1, function	Field device side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket Cable
Electrical connection 1, cable outlet	Straight, angled
Electrical connection 1, connector system	M12x1, A-coded to EN 61076-2-101 M8x1, A-coded, to EN 61076-2-104 Open end Diameter 8 mm, A-coded to EN 61076-2-104
Electrical connection 1, number of connections/cores	3 ...5
Electrical connection 1, used connections/cores	3 ...5
Electrical connection 1, type of mounting	Snap-locking Screw-type lock with 13 mm hexagon and longitudinal knurl Screw-type lock with hexagon A/F 9 mm and longitudinal knurl Rotatable
Electrical connection 1, compatible type of mounting	Compatible with latching lock Compatible with rotatable/non-rotatable screw-type lock
Electrical connection 1, terminal allocation	Pin 1 = BN Pin 2 = WH Pin 3 = BU Pin 4 = BK Pin 5 = GY

Feature	Value
Electrical connection 1, display	None Status indicator LED green Switching status indication, yellow LED for PNP N/O contact Switching status indication, yellow LED for NPN N/O contact
Electrical connection 2, function	Controller side
Electrical connection 2, design	Round
Electrical connection 2, connection type	Cable Plugs
Electrical connection 2, cable outlet	Straight Angled
Electrical connection 2, connector system	M12x1, A-coded to EN 61076-2-101 M8x1, A-coded to EN 61076-2-104 Open end
Electrical connection 2, number of connections/cores	3 ...5
Operational voltage range DC	0 V...250 V
Operational voltage range AC	0 V...250 V
Current rating at 40° C	4 A
Cable length	0.3 m...30 m
Cable characteristic	Suitable for energy chains/robot applications Abrasion-resistant Low adhesion Flame-retardant and self-extinguishing
Test conditions cable	Test conditions on request Torsional strength: > 300,000 cycles, $\pm 270^\circ/0.1$ m Flexural strength: > 50000 cycles, bending radius 5 mm Energy chain: > 5 million cycles, bending radius 28 mm
Cable structure	3 x 0.25 mm ² 4 x 0.25 mm ² 5 x 0.25 mm ²
Degree of protection	IP65 IP68 IP69K
Special characteristics	UV resistant Hydrolysis-resistant Resistant to cooling lubricants Resistant to microbes Oil resistant Ozone-resistant
Outdoor applications	Application areas with direct exposure to outdoor climatic influences Class D1 based on IEC 60654-1
Ambient temperature	-40 °C...85 °C
Note on ambient temperature	-40 - 50 °C for UL applications
Ambient temperature with moving cable	-20 °C...85 °C
Note on the ambient temperature with flexible cable installation	-20 - 50 °C for UL applications
Storage temperature	-25 °C...55 °C
Note on storage temperature	Temporarily during transport in packaging -40 ... 85 °C
Relative air humidity	Max. 93% at 40 °C
Nominal altitude of use	≤ 2000 m NHN
Overvoltage category	II
CE mark (see declaration of conformity)	To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK regulations for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Product corresponds to the internal product definition from Festo for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 4 according to ISO 14644-1

Feature	Value
Note on materials	CFC-free RoHS-compliant Cadmium-free Free of halogen Free of phosphoric acid ester
Corrosion resistance class CRC	1 - Low corrosion stress
Material housing	TPE-U(PUR)
Material screw-type lock	Die-cast zinc, nickel-plated
Material seals	FPM