


Mini slide DGST-20-10-E1A

Part number: 8078862

FESTO



Data sheet

Feature	Value
Stroke	10 mm
Piston diameter	20 mm
Operating mode, drive unit	Yoke
Cushioning	Elastomer cushioning, double-sided, stroke not adjustable
Mounting position	optional
Guide	Ball bearing cage guide
Design	Twin piston Yoke Piston rod Slide
Position detection	Via proximity switch
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi
Max. speed	0.5 m/s
Repetition accuracy	<= 0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...60 °C
Impact energy in end positions	0.2 J
Cushioning length	1 mm
Max. force Fy	1600 N
Max. force Fz	1600 N
Max. moment Mx	16 Nm
Max. moment My	18 Nm
Max. moment Mz	18 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	317 N

Feature	Value
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	377 N
Moving mass	440 g
Product weight	978 g
Type of mounting	With through-hole
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	HNBR
Material guide	POM TPE-E High-alloy steel
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel