


Compact cylinder AEN-S-6-5-A

Part number: 8080593

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 5 mm |
| Piston diameter | 6 mm |
| Cushioning | No cushioning |
| Mounting position | optional |
| Mode of operation | Pushing |
| Piston-rod end | Male thread |
| Design | Piston Piston rod |
| Variants | Piston rod at one end |
| Operating pressure | 0.25 MPa...0.8 MPa 2.5 bar...8 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C...60 °C |
| Impact energy in end positions | 0.006 J |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 4 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 13 N |
| Moving mass | 1.5 g |
| Product weight | 9.2 g |
| Type of mounting | With through-hole |
| Pneumatic connection | M3 |
| Note on materials | RoHS-compliant |
| Material cover | Wrought aluminium alloy |
| Material dynamic seals | NBR TPE-U(PU) |
| Material housing | Wrought aluminium alloy Anodised |
| Material piston rod | High-alloy stainless steel |