

# Compact cylinder AEN-S-16-10-A-P

Part number: 8092143

**FESTO**



## Data sheet

Feature	Value
Stroke	10 mm
Piston diameter	16 mm
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Pushing
Piston-rod end	Male thread
Design	Piston Piston rod
Variants	Piston rod at one end
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Impact energy in end positions	0.038 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	9.5 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	95 N
Moving mass for 0 mm stroke	6 g
Additional moving mass per 10 mm stroke	4 g
Basic weight for 0 mm stroke	32.5 g
Additional weight per 10 mm stroke	18 g
Type of mounting	With through-hole Via female thread With accessories Either:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Anodised wrought aluminium alloy
Material dynamic seals	NBR
Material housing	Anodised wrought aluminium alloy

Feature	Value
Material piston rod	High-alloy stainless steel