



Motor cable

NEBM-H6G4-E-25-Q13N-LE4

Part number: 8097205

FESTO



Data sheet

Feature	Value
Cable designation	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	Angular
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	Connection pattern H6, coded for motor
Electrical connection 1, number of connections/cores	4
Electrical connection 1, used connections/cores	4
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Cable
Electrical connection 2, connector system	Open end
Electrical connection 2, number of connections/cores	4
Electrical connection 2, used connections/cores	4
Operational voltage range DC	0 V...300 V
Operational voltage range AC	0 V...300 V
Current rating at 40° C	9.5 A
Immunity to surge	2 kV
Cable length	25 m
Cable characteristic	Suitable for energy chains
Test conditions cable	Test conditions on request
Bending radius, fixed cable	55 mm
Bending radius, moving cable	55 mm
Cable diameter	7.3 mm
Cable structure	4 x 0.79 mm ²
Nominal cross section conductor	0.79 mm ²
Conductor nominal cross section	AWG18
Wire ends	Wire ferrule
Degree of protection	IP20
Note on degree of protection	In assembled state
Ambient temperature	-25 °C...90 °C
Ambient temperature with moving cable	-25 °C...90 °C

Feature	Value
CE mark (see declaration of conformity)	To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK regulations for electrical equipment
LABS (PWIS) conformity	VDMA24364 zone III
Note on materials	RoHS-compliant
Pollution degree	3
Corrosion resistance class CRC	0 - No corrosion stress
Material cable sheath	PVC
Cable sheath colour	Black
Material housing	PA
Housing colour	White
Material insulating sheath	PVC