

Push-in fitting NPQE-DK-M5-Q3-P10

Part number: 8112966

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Mini |
| Nominal size | 2 mm |
| Type of seal on screwed plug | Sealing ring |
| Mounting position | optional |
| Design | Straight design Push-pull principle |
| Size of pack | 10 |
| Operating pressure complete temperature range | -0.095 MPa...0.8 MPa -0.95 bar...8 bar -13.775 psi...116 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Cleanroom class | Class 4 according to ISO 14644-1 |
| Ambient temperature | -5 °C...60 °C |
| Nominal torque | 0.8 Nm |
| Tolerance for nominal tightening torque | ± 5% |
| Product weight | 3 g |
| Type of mounting | Internal hexagon, size 2 mm |
| Pneumatic connection, port 1 | Male thread M5 |
| Pneumatic connection, port 2 | For tubing outer diameter of 3 mm |
| Colour of release ring | Blue |
| Note on materials | RoHS-compliant |
| Material housing | Brass, nickel-plated |
| Material thread seal | NBR High-alloy stainless steel |
| Material release ring | POM |
| Material tubing seal | NBR |
| Material tubing clamp component | Stainless steel |