


Pressure sensor SPAN-B-B11R-G18M-PN-L1+2.5S

Part number: 8114765

FESTO



Data sheet

Feature	Value
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Note on materials	RoHS-compliant
Measured variable	Relative pressure
Measurement method	Piezoresistive pressure sensor
Start value for pressure measuring range	-0.1 MPa -1 bar -14.5 psi
End value for pressure measuring range	1 MPa 10 bar 145 psi
Max. overload pressure	15 bar
Overload pressure	1.5 MPa 15 bar 217.5 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible
Media temperature	0 °C...50 °C
Ambient temperature	0 °C...50 °C
Accuracy in ± % FS	1.5 %FS
Repetition accuracy in ± %FS	0.3 %FS
Temperature coefficient in ± %FS/K	0.1 %FS/K
Switching output	PNP/NPN, switchable
Switching function	Window comparator Threshold value comparator
Switching element function	N/C or N/O contact, switchable
Max. output current	80 mA
Short circuit current rating	yes
Operational voltage range DC	10.8 V...30 V

Feature	Value
Reverse polarity protection	For all electrical connections
Electrical connection 1, connection type	Plugs
Electrical connection 1, connector system	Connection pattern L1J
Electrical connection 1, number of connections/cores	4
Type of mounting	Front panel mounting Via thread Via wall/surface bracket
Mounting position	optional
Pneumatic connection	Male thread G1/8
Product weight	31 g
Material housing	PA-reinforced
Material in contact with the medium	FPM Nickel-plated brass PA-reinforced
Display type	Illuminated LCD
Displayable units	MPa bar inHg kPa mmHg psi
Setting options	Teach-in Via display and keys
Protection against tampering	PIN code
Setting range threshold value	0 %...100 %
Setting range hysteresis	0 %...90 %
Degree of protection	IP40
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 4 according to ISO 14644-1