


Guided drive DFM-20-25-P-A-GF-F1A

Part number: 8118844

FESTO



Data sheet

| Feature | Value |
|---|--|
| Distance from centre of gravity of load to yoke plate xs | 50 mm |
| Stroke | 25 mm |
| Piston diameter | 20 mm |
| Operating mode, drive unit | Yoke |
| Cushioning | Elastic cushioning rings/plates at both ends |
| Mounting position | optional |
| Guide | Plain-bearing guide |
| Design | Guidance |
| Position detection | Via proximity switch |
| Variants | Metals with copper, zinc or nickel by mass as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils. |
| Operating pressure | 0.2 MPa...1 MPa 2 bar...10 bar |
| Max. speed | 0.8 m/s |
| Mode of operation | Double-acting |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Suitability for the production of Li-ion batteries | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 6 according to ISO 14644-1 |
| Ambient temperature | -20 °C...80 °C |
| Impact energy in end positions | 0.2 Nm |
| Max. force Fy | 354.7 N |
| Max. force Fy static | 354.7 N |
| Max. force Fz | 354.7 N |
| Max. force Fz static | 354.7 N |
| Max. moment Mx | 10.29 Nm |
| Max. torque Mx static | 10.29 Nm |
| Max. moment My | 3.37 Nm |

| Feature | Value |
|---|----------------------------|
| Max. torque M_y static | 3.37 Nm |
| Max. moment M_z | 3.37 Nm |
| Max. torque M_z static | 3.37 Nm |
| Max. permissible torque load M_x as a function of stroke | 1.47 Nm |
| Max. effective load dependent upon stroke at defined distance x_s | 28 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 141 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 188 N |
| Moving mass | 400 g |
| Product weight | 806 g |
| alternative connections | See product drawing |
| Pneumatic connection | M5 |
| Note on materials | RoHS-compliant |
| Material cover | Wrought aluminium alloy |
| Material seals | NBR |
| Material housing | Wrought aluminium alloy |
| Material piston rod | High-alloy stainless steel |