


Connecting cable NEBC-R3Z12G20-KH-5-N-SBS-RSG17-ET-S1

Part number: 8126916

FESTO



Data sheet

Feature	Value
Cable designation	Without inscription label holder
Product weight	680 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Angular
Electrical connection 1, connection type	Plug and socket strip
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	RJ45 and socket strip 12 pins, 2 rows
Electrical connection 1, number of connections/cores	20
Electrical connection 1, used connections/cores	14
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection 2, function	Controller side
Electrical connection 2, design	Round
Electrical connection 2, connection type	Hybrid plug
Electrical connection 2, cable outlet	Straight
Electrical connection 2, number of connections/cores	17
Electrical connection 2, used connections/cores	14
electrical connection 2, type of mounting	Threaded
Operational voltage range DC	0 V...24 V
Nominal operating voltage DC	24 V
Current rating at 40° C	11.7 A
Immunity to surge	6 kV
Shielding	no
Cable length	5 m
Cable characteristic	Standard
Test conditions cable	Test conditions on request
Bending radius, fixed cable	130 mm
Bending radius, moving cable	130 mm
Cable diameter	8 mm
Cable diameter tolerance	± 1 mm

Feature	Value
Cable structure	4 x (1 x 0.128 mm ²) + 10 x 0.128 mm ²
Nominal cross section conductor	0.128 mm ²
Degree of protection	IP65
Note on degree of protection	In assembled state
Ambient temperature	0 °C...40 °C
Ambient temperature with moving cable	0 °C...40 °C
Storage temperature	-20 °C...70 °C
CE mark (see declaration of conformity)	To EU Low Voltage Directive
LABS (PWIS) conformity	VDMA24364 zone III
Note on materials	RoHS-compliant
Pollution degree	3
Corrosion resistance class CRC	0 - No corrosion stress
Material cable sheath	TPE-U(PUR)
Cable sheath colour	Red
Material insulating sheath	PP