

# Radial gripper DHRC-32-A

Part number: 8128107

FESTO



## Data sheet

Feature	Value
Size	32
Max. replacement accuracy	0.2 mm
Max. opening angle	180 deg
Rotationally symmetrical	0.2 mm
Repetition accuracy, gripper	0.1 mm
Number of gripper jaws	2
Drive system	Pneumatic
Mounting position	optional
Mode of operation	Double-acting
Gripper function	Radial
Gripper force back-up	None
Design	Connection direction at side Force pilot operated motion sequence
Position detection	Via proximity switch
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi
Max. operating frequency of gripper	2 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	117 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	129 ms
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Total gripping torque at 0.6 MPa (6 bar, 87 psi), opening	725.6 Ncm
Total gripper torque, closing, 0.6 MPa (6 bar, 87 psi)	600.1 Ncm
Mass moment of inertia	3.105 kgcm <sup>2</sup>
Max. force on gripper jaw Fz static	210 N
Max. torque at gripper Mx static	12 Nm
Max. torque at gripper My static	8 Nm

Feature	Value
Max. torque at gripper Mz static	12 Nm
Product weight	716.5 g
Type of mounting	Direct mounting via through-hole Direct mounting via thread Via through-hole and dowel pin Via female thread and dowel pin Either:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover cap	Wrought aluminium alloy, anodised
Material housing	Anodised wrought aluminium alloy
Material gripper jaws	High-alloy steel