

Standards-based cylinder CRDSNU-20-10-P-A

Part number: 8152557

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 10 mm |
| Piston diameter | 20 mm |
| Piston rod thread | M8 |
| Cushioning | Elastic cushioning rings/plates at both ends |
| Mounting position | optional |
| Conforms to standard | ISO 6432 |
| Piston-rod end | Male thread |
| Design | Piston Piston rod Cylinder barrel |
| Position detection | Via proximity switch |
| Operating pressure | 0.1 MPa...1 MPa 1 bar...10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 3 - high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom class | Class 6 according to ISO 14644-1 |
| Suitable for use with food | See declaration of conformity |
| Ambient temperature | -20 °C...80 °C |
| Impact energy in end positions | 0.2 J |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 158 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 188 N |
| Moving mass for 0 mm stroke | 42 g |
| Additional moving mass per 10 mm stroke | 4 g |
| Basic weight for 0 mm stroke | 310 g |
| Additional weight per 10 mm stroke | 7 g |
| Type of mounting | With accessories |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS-compliant |

| Feature | Value |
|--------------------------|----------------------------|
| Material cover | High-alloy stainless steel |
| Material piston rod | High-alloy stainless steel |
| Material cylinder barrel | High-alloy stainless steel |