


# Mini slide

## EGSC-BS-KF-60-125-5P

Part number: 8162083

FESTO



## Data sheet

Feature	Value
Working stroke	125 mm
Size	60
Stroke reserve	0 mm
Reversing backlash theoretical	150 µm
Spindle diameter	12 mm
Spindle pitch	5 mm/U
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Electric mini slide With ball screw drive
Type of motor	Stepper motor Servo motor
Referencing	Positive fixed stop block Negative fixed stop block Reference switch
Spindle type	Ball screw drive
Position detection	Via proximity switch
Max. acceleration	5 m/s <sup>2</sup>
Max. rotational speed	3000 rpm
Max. speed	0.25 m/s
Repetition accuracy	±0.015 mm
Duty cycle	100%
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitability for the production of Li-ion batteries	Product corresponds to the internal product definition from Festo for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 9 according to ISO 14644-1
Sound pressure level	55 dB(A)
Degree of protection	IP40
Ambient temperature	0 °C...50 °C
Impact energy in end positions	0.04 mJ

Feature	Value
Note on the impact energy in the end positions	At maximum homing speed of 0.01 m/s
Dynamic basic load rating fixed bearing	13321 N
Dynamic basic load rating linear guide	13400 N
Dynamic basic load rating ball screw	5900 N
Idle torque at v <sub>max</sub>	0.125 Nm
Idle torque at v <sub>min</sub>	0.032 Nm
Max. force F <sub>y</sub>	4937 N
Max. force F <sub>z</sub>	4937 N
F <sub>y</sub> at theoretical life value of 100 km (only guide consideration)	13400 N
F <sub>z</sub> at theoretical life value of 100 km (only guide consideration)	13400 N
Max. moment M <sub>x</sub>	20 Nm
Max. moment M <sub>y</sub>	30 Nm
Max. moment M <sub>z</sub>	30 Nm
M <sub>x</sub> at theoretical life value of 100 km (only guide consideration)	107 Nm
M <sub>y</sub> at theoretical life value of 100 km (only guide consideration)	117 Nm
M <sub>z</sub> at theoretical life value of 100 km (only guide consideration)	117 Nm
Max. radial force at drive shaft	230 N
Max. feed force F <sub>x</sub>	250 N
Reference value effective load, horizontal	25 kg
Reference value effective load, vertical	25 kg
Static basic load rating ball screw	10600 N
Static basic load rating linear guide	26900 N
Mass moment of inertia J <sub>H</sub> per metre of stroke	0.11539 kgcm <sup>2</sup>
Mass moment of inertia J <sub>L</sub> per kg of working load	0.00633 kgcm <sup>2</sup>
Mass moment of inertia J <sub>O</sub>	0.06624 kgcm <sup>2</sup>
Feed constant	5 mm/U
Static basic load rating fixed bearing	7000 N
Reference service life	5000 km
Maintenance interval	Life-time lubrication
Moving mass for 0 mm stroke	675 g
Additional moving mass per 10 mm stroke	40 g
Product weight	2742 g
Basic weight for 0 mm stroke	1555 g
Additional weight per 10 mm stroke	95 g
Type of mounting	Via female thread Via centring sleeve With accessories Via cylindrical pin
Interface code, actuator	T42
Note on materials	RoHS-compliant
Material guide slide	Rolled steel
Material guide rail	Rolled steel
Material housing	Anodised wrought aluminium alloy
Material yoke plate	Anodised wrought aluminium alloy
Material piston rod	High-alloy stainless steel
Material slide	Anodised wrought aluminium alloy
Material spindle nut	Rolled steel
Material spindle	Rolled steel