


Plug

NECB-S-M8G4-C2-D

Part number: 8162300

FESTO



Data sheet

| Feature | Value |
|--|---|
| Conforms to standard | EN 61076-2-104 |
| Approval | c UL us listed (OL) |
| Certificate issuing authority | UL E474609 |
| Frequency of connection | 100 |
| Cable outlet | Straight |
| Product weight | 8 g |
| Instructions on use | Only energy-limited circuits with a maximum current of 4 A at a max. open circuit voltage of 30 V DC are permissible for supplying electrically actuated valves from Festo. |
| Electrical connection 1, function | Controller side |
| Electrical connection 1, design | Round |
| Electrical connection 1, connection type | Plugs |
| Electrical connection 1, connector system | M8x1, A-coded, to EN 61076-2-104 |
| Electrical connection 1, number of connections/cores | 4 |
| Electrical connection 1, used connections/cores | 4 |
| Electrical connection 1, type of mounting | Screw-type lock with hexagon A/F 9 mm and longitudinal knurl Rotatable |
| Electrical connection 1, compatible type of mounting | Compatible with rotatable/non-rotatable screw-type lock |
| Electrical connection 2, function | Field device side |
| Electrical connection 2, connection type | 2x cable |
| Electrical connection 2, connector system | Screw terminal |
| Electrical connection 2, number of connections/cores | 4 |
| Electrical connection 2, used connections/cores | 4 |
| Operational voltage range DC | 0 V...60 V |
| Operational voltage range AC | 0 V...48 V |
| Current rating at 40° C | 4 A |
| Immunity to surge | 1.5 kV |
| Protective conductor connection | Not available |
| Cable fitting | M14 |
| Cable diameter | 2 mm...3.8 mm |

| Feature | Value |
|----------------------------------|---|
| Note on the cable diameter | One cable through-feed for diameters 5.0 – 7.6 mm Two cable through-feeds for diameters 2.0 – 3.8 mm |
| Connection cross section | 0.14 mm ² ...0.75 mm ² |
| Note on connection cross-section | 0.1 mm ² with wire ferrule |
| Degree of protection | IP65 IP67 |
| Note on degree of protection | In assembled state |
| Ambient temperature | -25 °C...90 °C |
| Note on ambient temperature | Note derating |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Note on materials | RoHS-compliant |
| Pollution degree | 3 |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| Material housing | PA66-GF30 |
| Housing colour | Black |
| Material screw-type lock | Die-cast zinc, nickel-plated |
| Material screws | Nickel-plated steel |
| Material seals | FPM |
| Material electrical contact | Brass, nickel-plated and gold-plated |