


Shock absorber
DYEF-G8-M10-Y1F
Part number: 8160238

FESTO



Data sheet

Feature	Value
Size	M10
Stroke	3.7 mm
Cushioning	Elastic cushioning rings/pads at both ends with metal fixed stop
Mounting position	optional
Position detection	Without
Max. impact speed	0.8 m/s
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Cushioning length	3.7 mm
Max. tightening torque	3 Nm
Max. energy consumption per stroke	0.06 J
Product weight	37.6 g
Type of mounting	Via threaded sleeve
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	High-alloy steel