


Semi-rotary drive DRRS-16-180-FH-PA

Part number: 8163609

FESTO



Data sheet

Feature	Value
Size	16
Cushioning angle	19.5 deg
Setting range of swivel angle for each end position	+10/-100 deg
Axial eccentricity poppet valve	0.07 mm
Swivel angle	180 deg
Min. swivel angle	45 deg
Max. swivel angle	200 deg
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Design	Rack and pinion
Position detection	Via proximity switch
Operating pressure	0.3 MPa...0.8 MPa 3 bar...8 bar
Repetition accuracy	0.07 deg
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Suitability for the production of Li-ion batteries	Product corresponds to the internal product definition from Festo for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 9 according to ISO 14644-1
Storage temperature	-20 °C...60 °C
Ambient temperature	0 °C...60 °C
Theoretical torque at 0.6 MPa (6 bar, 87 psi)	2.1 Nm
Permissible mass moment of inertia	0.008 kgm ²
Max. bending moment	4 Nm
Max. axial load static	140 N
Product weight	630 g

Feature	Value
Type of mounting	Via mounting kit With through-hole Via female thread Either:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material seals	NBR TPE-U(PU)
Material housing	Anodised aluminium
Flange shaft material	Wrought aluminium alloy
Pinion material	Tempered steel