


## Sub-base kit DADP-SP-G9-6-R

Part number: 8173532

**FESTO**



## Data sheet

Feature	Value
Size	6
Mounting position	optional
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Suitability for the production of Li-ion batteries	Product corresponds to the internal product definition from Festo for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...60 °C
Max. stop force	60 N
Max. tightening torque	0.3 Nm
Tolerance for tightening torque	± 15 %
Product weight	24 g
Type of mounting	Direct mounting via thread
Note on materials	RoHS-compliant
Material stops	High-alloy steel
Material seals	NBR
Material plate	Anodised wrought aluminium alloy
Material screws	Steel