


Limit switch box SRBK-CA4-YR90-N-1-P-M12

Part number: 8182182

FESTO



Data sheet

Feature	Value
CE mark (see declaration of conformity)	To EU EMC Directive To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK regulations for electrical equipment
Note on materials	RoHS-compliant
Measured variable	Position
Measuring principle	Inductive
Sensing range	0 deg...90 deg
Ambient temperature	-20 °C...70 °C
Switching output	PNP
Switching element function	N/O contact
Max. output current DC	100 mA
Voltage drop	3 V
Off-state current	0 mA...0.5 mA
Short circuit current rating	Pulsed
Operational voltage range DC	10 V...30 V
No-load supply current	15 mA
Reverse polarity protection	For all electrical connections
Microswitch type	P&F NBB2-V3-E2
Electrical connection	M12x1
Electrical connection 1, connection type	Plugs
Electrical connection 1, cable outlet	Straight
Electrical connection 1, design	Round
Electrical connection 1, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 1, number of connections/cores	8
Cable fitting	M20x1.5

Feature	Value
Dimensions (W x L x H)	143 mm x 85 mm x 128 mm 143 mm x 85 mm x 138 mm 143 mm x 85 mm x 158 mm 159 mm x 85 mm x 128 mm 159 mm x 85 mm x 138 mm
Connection point for positioner and position sensor conforms to standard	VDI/VDE 3845 size AA 1 VDI/VDE 3845 size AA 2 VDI/VDE 3845 size AA 3
Mounting position	optional
Product weight	500 g
Housing colour	Black
Material housing	PA
Material seals	NBR
Material shaft	PA
Material screws	Stainless steel
Material mounting bracket	PA
Material snap ring	High-alloy stainless steel
Protective cap material	PC
Switching status indication	Optical
Position indicator	Yellow/red
Setting range of angular detection	0 deg...90 deg
Storage temperature	-20 °C...50 °C
Degree of protection	IP66 IP67
Shock resistance	Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Pollution degree	3