


Shock absorber DYSD-Q13-5-5-Y1F-Y9

Part number: 8199039

FESTO



Data sheet

Feature	Value
Size	5
Stroke	5 mm
Cushioning	Self-adjusting
Mounting position	optional
Position detection	Without
Max. impact speed	0.5 m/s
Reset time at room temperature	0.2 s
Reset time at min. ambient temperature	1 s
Mode of operation	Pushing Single-acting
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production according to the Festo internal definition of the degree of severity F1A with restrictions regarding the use of Cu/Zn/Ni
Ambient temperature	-10 °C...60 °C
Cushioning length	5 mm
Max. stop force	180 N
Max. tightening torque	2 Nm
Max. energy consumption per stroke	1 J
Max. energy consumption per hour	2400 J
Reset force	5 N
Min. insertion force	18 N
Product weight	12 g
Load range	8 kg
Type of mounting	Via lock nut
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	High-alloy steel
Material piston rod	High-alloy steel
Material nut	High-alloy steel