



Parallel gripper HGPD-63-A-G2

Part number: 1132956

FESTO

With gripping force backup when closing...-G2.



Data sheet

Feature	Value
Size	63
Stroke per gripper jaw	16 mm
Max. replacement accuracy	≤ 0.2 mm
Max. angular gripper jaw backlash ax,ay	≤ 0.1 deg
Max. gripper jaw backlash Sz	≤ 0.02 mm
Rotationally symmetrical	≤ 0.2 mm
Repetition accuracy, gripper	≤ 0.05 mm
Number of gripper fingers	2
Drive system	pneumatic
Assembly position	Any
Mode of operation	double-acting
Gripper function	Parallel
Gripper force back-up	On closing
Design structure	Inclined plane guided motion sequence
Position detection	For proximity sensor
Working pressure	4 ... 8 bar
Working pressure, sealing air	0 ... 0.5 bar
Max. operating frequency of gripper	≤ 2 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	294 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	185 ms
Max. mass per external gripper finger	1,340 g
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Protection class	IP65
Ambient temperature	5 ... 60 °C
Mass moment of inertia	116.19 kgcm ²
Max. torque at gripper Mx static	120 Nm
Max. torque at gripper My static	80 Nm
Max. torque at gripper Mz static	65 Nm
Lubrication interval for guide components	5,000,000 Mio SP
Product weight	3,998 g
Mounting type	Internal thread and centering sleeve With through-hole and centering sleeve With through-hole and dowel pin With internal thread and dowel pin Optional
Pneumatic connection, sealing air	M5
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material cover cap	High alloy steel, non-corrosive
Material housing	Anodised aluminium
Material gripper jaws	Steel, hardened