


# Stepper motor EMMS-ST-87-L-S-G2

Part number: 1370490

★ Core product range

Without gearing, without brake.

FESTO



## Data sheet

Feature	Value
Ambient temperature	-10 ... 50 °C
Storage temperature	-20 ... 70 °C
Relative air humidity	0 - 85 %
Conforms to standard	IEC 60034
Insulation protection class	B
Thermal class according to EN 60034-1	B
Rating class according to EN 60034-1	S1
Protection class	IP54
Electrical connector system	Plug
Materials note	Conforms to RoHS
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Authorization	RCM Mark c UL us - Recognized (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Nominal operating voltage DC	48 V
Motor holding torque	9.3 Nm
Max. speed	430 1/min
Stepper angle at full step	1.8 deg
Stepper angle tolerance	±5 %
Nominal motor current	9.5 A
Voltage constant, phase	77.2 mVmin
Winding resistance phase	0.23 Ohm
Winding inductance phase	2.7 mH
Mass moment of inertia of rotor	3 kgcm <sup>2</sup>
Overall mass moment of inertia at power take-off	3 kgcm <sup>2</sup>
Product weight	4,200 g
Permissible axial shaft load	65 N
Permissible radial shaft load	200 N
Brake holding torque	2 Nm