



# Standard cylinder DNU-40- -PPV-A-S2

Part number: 14187

FESTO

As per ISO 15552, with profile cylinder barrel, for proximity sensing,  
with adjustable cushioning at both ends.

Discontinued, available through 2008



Exemplary representation

## Data sheet

Feature	Value
Stroke	1 ... 2,000 mm
Piston diameter	40 mm
Piston rod thread	M12x1,25
Based on the standard	ISO 6431
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Assembly position	Any
Piston-rod end	Male thread
Design structure	Piston Piston rod
Position detection	For proximity sensor
Variants	S2: through piston rod
Operating pressure	0.6 ... 12 bar
Mode of operation	double-acting
Operating medium	Dried compressed air, lubricated or unlubricated
Corrosion resistance classification CRC	2
Ambient temperature	-20 ... 80 °C
Authorization	Germanischer Lloyd
Cushioning length	21 mm
Theoretical force at 6 bar, return stroke	586 N
Theoretical force at 6 bar, advance stroke	586 N
Mounting type	with accessories
Pneumatic connection	G1/4
Materials information for cover	Aluminum
Materials information for seals	TPE-U(PU)
Materials information for piston rod	High alloy steel
Materials information for cylinder barrel	Wrought Aluminum alloy Anodized