



Intermediate-position module DADM-EP-G6-16

Part number: 1478121

FESTO



Data sheet

Feature	Value
Size	16
Assembly position	Any
Design structure	guided motion sequence
Position detection	For proximity sensor
Working pressure	3 ... 6 bar
Max. impact speed	0.8 m/s
Max. swivel time	150 ms
Repetition accuracy	±0,02 mm
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	0 ... 60 °C
Max. stop force	1,100 N
Product weight	340 g
Mounting type	With through-hole and centering sleeve
Pneumatic connection	M5
Materials note	Conforms to RoHS
Material seals	PU
Material housing	Wrought Aluminum alloy
Material lever	High alloy steel, non-corrosive