

Condensate drain WA-2

Part number: 152810

FESTO

Automatic



Data sheet

Feature	Value
Type of actuation	mechanical
Assembly position	Vertical +/- 5°
Manual override	Pushing
Condensate drain	fully automatic
Design structure	External, mechanical, fully automated
Measured variable	Fill-level
Valve function	2/2 open, monostable
Working pressure	1.5 ... 14 bar
Operating medium	Water
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 60 °C
Medium temperature	0 ... 50 °C
Ambient temperature	0 ... 50 °C
Product weight	92 g
Mounting type	Line installation
Condensate drain connection	PK-4
Pneumatic connection	M9
Material housing	Wrought Aluminum alloy