



Proximity Sensor SME-1-S-LED-24-B

Part number: 150851

FESTO



Data sheet

Feature	Value
Design	Block design
Authorization	RCM Mark
CE symbol (see declaration of conformity)	according to EU-EMV guideline in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Materials note	Conforms to RoHS
Measured variable	Position
Measuring principle	Reed magnetic
Ambient temperature	-20 ... 70 °C
Repetition accuracy	0.2 mm
Switch output	with contact, bipolar
Switching element function	Normally open contact
Switch-on time	≤ 0.5 ms
Max. output current	1 A
Max. contact rating AC	27 VA
Max. contact rating DC	27 W
Short circuit strength	No
Overload withstand capability	Not available
Operating voltage range AC	12 ... 27 V
Operating voltage range DC	12 ... 27 V
Polarity protected	No
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection 1, number of pins/wires	3
Connector exit direction	axial
Mounting type	with accessories
Assembly position	Any
Product weight	45 g
Housing color	Black
Material housing	Epoxy resin PET Steel steel, galvanized Zinc die-casting
Operating status display	Yellow LED
Ambient temperature with flexible cable installation	-5 ... 70 °C
Protection class	IP67
PWIS conformity	VDMA24364-B2-L