


# Motor controller CMMO-ST-C5-1-DION

Part number: 1512317  
Product to be discontinued

For use as position controller.

Type to be discontinued. Available until 2026. See Support Portal for alternative products.

FESTO



## Data sheet

Feature	Value
Mounting type	On subbase Tightened with top-hat rail
Product weight	290 g
Display	Seven-segment display
Authorization	RCM Mark c UL us - Listed (OL)
KC mark	KC-EMV
CE symbol (see declaration of conformity)	according to EU-EMV guideline according to EU machines guideline in accordance with EU RoHS directive
Certificate issuing department	01/205/5252.02/20 TÜV Rheinland
Storage temperature	-25 ... 75 °C
Ambient temperature	0 ... 50 °C
UL ambient temperature	0 ... 40 °C
Relative air humidity	0 - 90 % non-condensing
Protection class	IP40
Materials note	Conforms to RoHS
PWIS conformity	VDMA24364-B2-L
Nominal current, load supply	6 A
Peak current, load supply	8 A
Mains filter	Integrated
Nominal voltage, load supply DC	24 V
Max. intermediate circuit voltage, DC	28 V
Braking resistance	15 Ohm
Braking resistance pulse power	0.1 kVA
Nominal DC voltage, logic power supply	24 V
Permissible range, logic voltage	± 15 %
Nominal current, logic supply	0.3 A
Nominal output current	5.7 A
Controller operating mode	PWM-MOSFET power output stage Cascade controller with P position controller PI speed controller Proportional and integral controller for electricity
Adjustable current reduction	Using software
Step adjustment	Using software
Protective function	I <sup>2</sup> t monitoring Temperature monitoring Current monitoring

<b>Feature</b>	<b>Value</b>
	Voltage failure detection Drag error monitoring Software end-position detection
Nominal current adjustment	Using software
Parameters configuring interface	Ethernet
Ethernet, supported protocols	TCP/IP
Process interface	I/O coupling For 32 traversing records
Rotor position sensor	Encoder
Position sensor	Encoder
Encoder interface input, characteristics	RS422
Number of digital logic inputs	11
Input circuit logic	NPN (negative switching)
Logic input characteristics	galvanically connected to logic potential
Specification, logic input	Based on IEC 61131-2
Logic input working range	24 V
Number of 24 V DC digital logic outputs	11
Switching logic, outputs	NPN (negative switching)
Digital logic output characteristics	Freely configurable to a given extent Not electrically isolated
Max. current, digital logic outputs	100 mA
Safety function	Safe torque off (STO)
Safety Integrity Level (SIL)	Safe torque off (STO)/SIL 3
Performance level (PL)	Safe torque off (STO)/category 3, Performance Level e