

# Push-in T-fitting QSTL-1/8-3/16-U


Part number: 153711

FESTO

rotatable by 360°, male thread with external hexagon.

This product is only available if ordered from the Festo Corporation, USA.

Type to be discontinued. Available until 2011.



## Data sheet

| Feature                                 | Value                              |
|---|------------------------------------|
| Size                                    | Standard                           |
| Type of seal on screw-in stud           | coating                            |
| Assembly position                       | Any                                |
| Container size                          | 1                                  |
| Design structure                        | Push/pull principle                |
| Working pressure                        | -0.95 ... 10 bar                   |
| Temperature dependent working pressure  | -0.95 ... 10 bar                   |
| Operating medium                        | Filtered compressed air<br>Vacuum  |
| Corrosion resistance classification CRC | 1                                  |
| Ambient temperature                     | -10 ... 60 °C                      |
| Authorization                           | Germanischer Lloyd                 |
| Max. tightening torque                  | 8 Nm                               |
| Number of outputs                       | 2                                  |
| Number of supply lines                  | 1                                  |
| Pneumatic connection, supply line       | Male thread NPT1/8-27              |
| Pneumatic connection, output            | for tubing, 3/16" outside diameter |
| color of release ring                   | Grey                               |
| Materials note                          | Conforms to RoHS                   |
| Materials information, housing          | PBT                                |
| Release ring material data              | POM                                |
| Materials information for tubing seal   | NBR                                |
| Hose clamping segment material data     | High alloy steel, non-corrosive    |