


Bus node CTEU-CC

Part number: 1544198

FESTO



Data sheet

Feature	Value
Protocol	CC-Link
Dimensions W x L x H	40 mm x 91 mm x 50 mm
Grid dimension	40 mm
Mounting type	On electrical interface On electrical connection block
Product weight	90 g
Ambient temperature	-5 ... 50 °C
Storage temperature	-20 ... 70 °C
Protection class	IP65 IP67
Note on degree of protection	in assembled condition Unused connections sealed
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364 zone III
CE symbol (see declaration of conformity)	according to EU-EMV guideline in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
KC mark	KC-EMV
Authorization	RCM Mark c UL us - Listed (OL)
Materials note	Conforms to RoHS
Material housing	PA
Product-specific LED display	PS: operating voltage for electronics and load supply X1: System status module I port 1 X2: System status module I port 2
Bus-specific LED display	Err: faulty data transmission Run: bus active
Diagnosis	Communication error System diagnostics Undervoltage
Control elements	DIL switches
Note regarding fieldbus interface	Optional connection technology with accessories: Open Style (screw terminal, 5-pin, degree of protection IP20)
Fieldbus interface	Serial interface
Fieldbus interface, protocol	CC-LINK®
Fieldbus interface, type of connection	Plug socket
Fieldbus interface, connection technology	Sub-D
Fieldbus interface, number of pins/wires	9
Fieldbus interface, electrical isolation	Yes
Fieldbus interface, transmission rate	156 - 10000 kbit/s
Maximum address volume for inputs	16 Byte
Maximum address volume for outputs	16 Byte
Parameters configuring	Activating diagnostics Fail-safe mode and idle response
Internal cycle time	1 ms per 1 byte of user data

Feature	Value
Additional functions	System status can be represented using process data
Power supply, function	Electronics and load
Power supply, type of connection	Plug
Power supply, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Power supply, number of pins/wires	5
Operating voltage range DC	18 ... 30 V
Nominal operating voltage DC	24 V
Max. power supply	4 A
Intrinsic current consumption at operating voltage	Typ. 70 mA