

# Servomotor EMMS-AS-100-M-HS-RR-S1

Part number: 1562950

FESTO

Without gear unit.



## Data sheet

| Feature  | Value  |
|--|--|
| Ambient temperature                              | -40 ... 40 °C  |
| Storage temperature                              | -20 ... 60 °C  |
| Relative air humidity                            | 0 - 90 %   |
| Conforms to standard                             | IEC 60034  |
| Insulation protection class                      | F  |
| Rating class according to EN 60034-1             | S1   |
| Temperature monitoring                           | PTC resistor   |
| Protection class                                 | IP65   |
| Electrical connector system                      | Plug   |
| Materials note                                   | Conforms to RoHS   |
| Corrosion resistance classification CRC          | 2 - Moderate corrosion stress  |
| Authorization                                    | RCM Mark<br>c UL us - Recognized (OL)                                  |
| CE symbol (see declaration of conformity)        | according to EU-EMV guideline<br>according to EU low voltage guideline |
| Nominal operating voltage DC                     | 565 V  |
| Nominal voltage DC                               | 565 V  |
| Type of winding switch                           | Star inside  |
| Number of pole pairs                             | 6  |
| Standstill torque                                | 8.01 Nm  |
| Nominal torque                                   | 5.63 Nm  |
| Peak torque                                      | 22.1 Nm  |
| Nominal rotary speed                             | 3,400 1/min  |
| Max. speed                                       | 4,030 1/min  |
| Nominal motor power                              | 2,000 W  |
| Nominal motor current                            | 3.4 A  |
| Peak current                                     | 15 A   |
| Motor constant                                   | 1.652 Nm/A   |
| Voltage constant, phase-to-phase                 | 99.15 mVmin  |
| Phase-phase winding resistance                   | 3.25 Ohm   |
| Phase-phase winding inductance                   | 12.3 mH  |
| Overall mass moment of inertia at power take-off | 4.7 kgcm <sup>2</sup>  |
| Product weight                                   | 7,140 g  |
| Permissible axial shaft load                     | 150 N  |
| Permissible radial shaft load                    | 570 N  |
| Rotor position sensor                            | Resolver   |
| Rotary position encoder interface                | SIN/COS analogue signal  |
| Rotary position encoder measuring principle      | Inductive  |
| MTTF, subcomponent                               | 114 years, rotary position encoder                                     |
| MTTFd, subcomponent                              | 228 years, rotary position encoder                                     |