



Compact cylinder

AEVU-12- -P-A-S26

Part number: 156240
 Classic - do not use for new projects

For proximity sensing, piston-rod end with female thread.
 Modern alternatives can be found by entering the first four characters of the type code in the search field.
 Type to be discontinued. Available until 2022. See Support Portal for alternative products.



Data sheet

Feature	Value
Stroke	1 ... 10 mm
Piston diameter	12 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Mode of operation	single-acting
Piston-rod end	Female thread
Design structure	Piston Piston rod
Position detection	For proximity sensor
Variants	Through piston rod Heat resistant seals, max. 120°C
Operating pressure MPa	0.15 ... 1 MPa
Working pressure	1.5 ... 10 bar
Operating pressure	21.75 ... 145 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	0 ... 120 °C
Impact energy in end positions	0.07 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	42 N
Mounting type	with through hole with accessories Optional
Pneumatic connection	M5
Material of flange screw	High alloy steel, non-corrosive
Material cover	Wrought Aluminum alloy
Material of dynamic seals	FPM
Material piston rod	High alloy steel, non-corrosive
Material cylinder barrel	Wrought Aluminum alloy