

Servomotor EMMS-AS-55-S-HS-TM-S1

Part number: 1569773

FESTO

Without gear unit.



Data sheet

Feature	Value
Ambient temperature	-10 ... 40 °C
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 90 %
Conforms to standard	IEC 60034
Insulation protection class	F
Rating class according to EN 60034-1	S1
Temperature monitoring	PTC resistor
Protection class	IP65
Electrical connector system	Plug
Materials note	Conforms to RoHS
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Authorization	RCM Mark c UL us - Recognized (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline according to EU low voltage guideline
Nominal operating voltage DC	565 V
Nominal voltage DC	565 V
Type of winding switch	Star inside
Number of pole pairs	4
Standstill torque	0.46 Nm
Nominal torque	0.31 Nm
Peak torque	1.62 Nm
Nominal rotary speed	7,600 1/min
Max. speed	9,840 1/min
Nominal motor power	246 W
Nominal motor current	0.49 A
Peak current	2.7 A
Motor constant	0.635 Nm/A
Voltage constant, phase-to-phase	40.58 mVmin
Phase-phase winding resistance	56.9 Ohm
Phase-phase winding inductance	38.1 mH
Overall mass moment of inertia at power take-off	0.11 kgcm ²
Product weight	1,300 g
Permissible axial shaft load	75 N
Permissible radial shaft load	140 N
Rotor position sensor	Absolute multi-turn encoder
Rotary position encoder interface	EnDat 22
Rotary position encoder measuring principle	Inductive
Rotary position encoder resolution	19 Bit
MTTF, subcomponent	76 years, rotary position encoder
MTTFd, subcomponent	152 years, rotary position encoder