


Servomotor EMMS-AS-55-MK-HS-TSB

Part number: 1569817

FESTO

Without gear unit.



Data sheet

Feature	Value
Ambient temperature	-10 ... 40 °C
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 90 %
Conforms to standard	IEC 60034
Insulation protection class	F
Rating class according to EN 60034-1	S1
Temperature monitoring	PTC resistor
Protection class	IP54
Shaft design Featherkey	DIN 6885 A 3 x 3 x 14
Electrical connector system	Plug
Materials note	Conforms to RoHS
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Authorization	RCM Mark c UL us - Recognized (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline according to EU low voltage guideline
Nominal operating voltage DC	565 V
Nominal voltage DC	565 V
Type of winding switch	Star inside
Number of pole pairs	4
Standstill torque	0.99 Nm
Nominal torque	0.68 Nm
Peak torque	3.8 Nm
Nominal rotary speed	6,600 1/min
Max. speed	7,750 1/min
Nominal motor power	470 W
Nominal motor current	0.8 A
Peak current	4.9 A
Motor constant	0.829 Nm/A
Voltage constant, phase-to-phase	51.54 mVmin
Phase-phase winding resistance	31.3 Ohm
Phase-phase winding inductance	29.3 mH
Overall mass moment of inertia at power take-off	0.245 kgcm ²
Product weight	1,700 g
Permissible axial shaft load	75 N
Permissible radial shaft load	150 N
Rotor position sensor	Absolute single turn encoder
Rotary position encoder interface	EnDat 22
Rotary position encoder measuring principle	Inductive
Rotor position encoder resolution	18 Bit
Brake holding torque	0.8 Nm
Operating voltage DC for brake	24 V
Power consumption, brake	10 W

Feature	Value
Mass moment of inertia of brake	0.02 kgcm ²
Switching cycles, holding brake	10 million idle actuations (without friction work)
MTTF, subcomponent	76 years, rotary position encoder 11416 years, holding brake
MTTFd, subcomponent	152 years, rotary position encoder